


CONTROLLER
MODELS
4004, 4006
& 4008



* IMPORTANT
IF RKIT IS CONNECTED TO ANY
CIRCUIT OVER 24-VOLTS IT MUST BE
LOCATED IN A SEPARATE "HIGH
VOLTAGE" JUNCTION BOX.

TO LIGHTING SYSTEM PUMP
OR OTHER AC/DC POWERED
EQUIPMENT.

DRY SPLICE
CONNECTORS

LEMA MICROPOWER
ACTUATOR

TO
SPRINKLERS

6

TYPICAL SYSTEM INSTALLATION LEIT 4000
USING 1600HE SERIES ACTUATOR